



Packing Information

SJ-4 Package, TN Suffix




Terminals:4
 Spread
 Untrimmed
 Unformed (flat)
 Case top flat
 Non-JEDEC Standard



- Embossed tape and reel
- 800 devices per 13 in. reel
- 25 min. trailer pockets
- 75 min. leader pockets

- Branded face outward
- Device body on right side
- Elongated sprocket holes on left side
- Pin 1 on trailing device edge




Access hole and hub configuration may vary at supplier discretion within limits shown

Dimensions in mm

Type	A	B	C	D	N
Plastic 13 in.	330 (Nom)	1.5 (Min)	13 ^{+0.5} _{-0.2}	20.2 (Min)	102 (Nom)
W₁ (inside, at Hub)			32.4 (Min)		
W₂ (outside, at Hub)			38.4 (Max)		

Reference EIA 481




Dimensions in mm, may vary with supplier

Carrier Tape			Cover Tape
W: 44.00 ±.3	D ₀ : 1.50 +.1/-0	A ₀ : 8.40	W _c : 37.50 T _c : 0.061 (0.1 MAX)
E: 1.75 ±.1	P ₀ : 4.00 ±.1	B ₀ : 30.00	
F: 20.20 ±.15	P ₁ : 12.00 ±.1	K ₀ : 6.00	
T: 0.30 (0.5 MAX)	P ₂ : 2.00 ±.15	K ₁ : 2.30	
	S _c : 40.40 ±.1	K ₂ : 3.00	
		D ₁ : 2.00 MIN	


1. Pocket centerlines to cavity center, not to pocket detection hole.
2. A₀ and B₀ measured 0.3mm above bottom of pocket.

Reference EIA 481



Reference EIA 481

SJ-4 Package, TN Suffix



Carton Dimensions (mm)

Type	Length	Width	Height	Inner Carton Standard Quantity	Outer Carton Standard Quantity
TC17	364	348	56	800	--
TC18A	379	188	365	--	2400
TC18B	379	368	365	--	4800
TC17A	556	403	400	--	7200

* Carton Details pertain only to Full Standard Increments. Partial orders will only be provided for samples or due to exceptional circumstances. Partial orders may not be packed according to Carton Details but may require protective filler, empty inner boxes or other packing modifications.

SJ-4 Package, TN Suffix

Reel Production Label [A]
28.58mm x 101.6mm

Box Flap Label [B]
28.58mm x 101.6mm



Part (P)	A123456XXX-XXXXXXXX-XXXXXXXX
Mfr PN (1P)	A123456-XXX-XXX
Qty (Q)	1000
Lot (1T)	1234567XXX Qty (1Q) 1000
Lot 2 (2T)	N/A Qty (2Q) 0

Moisture Sensitive Device
Peak Reflow 260°C

MS-Level (13E) 2

Reel _____ Date (12D) 2019-01-01





Part (P)	A123456XXX-XXXXXXXX-XXXXXXXX
Mfr PN (1P)	A123456-XXX-XXX
Qty (Q)	1000
Lot (1T)	1234567XXX Qty (1Q) 1000
Lot 2 (2T)	N/A Qty (2Q) 0

Moisture Sensitive Device
Peak Reflow 260°C

MS-Level (13E) 2

Reel _____ Date (12D) 2019-01-01




1D Production Label [C]
63.5mm x 101.6mm

Inner Carton Label [D]
101.6mm x 165.1mm

00000000

Allegro MicroSystems
Manchester, NH 03103 USA



Cust PN: 999999XXX-XXX99999XX_000000000



Mfr PN: 999999XXX-XXX99999XX_000000000




Alg In: 000000XXX-XXX00000XX



Lot 1: 1234567XXX Qty 1: 10000



Lot 2: 1234567XXX Qty 2: 5000



D/C: 1234 Total Qty: 15000





ALLEGRO microsystems Manchester, NH 03103, USA (4L) Made In United States

(P) Customer Part
A12345XXX-XXXXXXXX-000000000



(1K) Sales Order
00000000



(1P) Manufacturer Part
A12345XXX-XXXXXXXX-000000000



(9D) Date Code
1234



(1T) Lot
1234567XXX



(Q) Quantity
100000



(K) Purchase Order
000000000-000000000



(16K) Delivery
00000000





Outer Carton Label [E]
101.6mm x 165.1mm

Outer Carton Address Label [F]
101.6mm x 165.1mm

ALLEGRO microsystems Manchester, NH 03103, USA (4L) Made In United States

(P) Customer Part
A12345XXX-XXXXXXXX-000000000



(1K) Sales Order
00000000



(1P) Manufacturer Part
A12345XXX-XXXXXXXX-000000000



(Q) Quantity
100000



(K) Purchase Order
000000000-000000000



(16K) Delivery
00000000





ALLEGRO microsystems

Ship To (Shipping Mark):
Allegro MicroSystems, LLC
ATTN: Corporate Label Team
955 Perimeter Rd
Manchester, NH 03103



Package 1 / 1

* Label examples are shown for content purposes only. Labels are not shown to scale. Given label dimensions are approximate. As required, the necessary compliance symbols on the labels will meet the ship to country regulations.

SJ-4 Package, TN Suffix

Revision History

Revision No.	Date	ECN No.	Description
0	2016-09-29	OI	ORIGINAL RELEASE
1	2017-10-23	CR-2017-03697	UPDATE PACKAGE ILLUSTRATION. ADD OUTER CARTON ADDRESS LABEL. ADD APPROX LABEL DIMENSIONS.
2	2018-10-19	CR-2018-04291	UPDATE PACKAGE GRAPHIC. UPDATE ORIENTATION GRAPHIC. UPDATE LABEL GRAPHICS (1D, INNER, OUTER, ADDRESS). UPDATE COPYRIGHT DATE. UPDATE ALLEGRO ADDRESS.
3	2021-10-18	CR-2021-03368	UPDATE TO NEW FORMAT. UPDATE LABEL GRAPHICS.

This document provides reference information that can be used to identify leadform and packing options offered by Allegro MicroSystems. This information is for reference only, and not for tooling use. This information is subject to change without notice. Packing and labelling for shipment may vary with device type, quantities, and other conditions; specifications may vary with contract terms and availability.

Packing options vary according to the individual device being offered. Refer to the device datasheet (visit our website at: www.allegromicro.com) for a listing of packing options for that device. Not all options are available for any particular package designation or device type, and provision of certain configurations may be subject to minimum volume or NCNR (noncancellation, nonreturn) limitations. Contact your local Allegro field service representative for additional information.

For more information on the physical appearance of device packages and leadforms, refer to the device datasheet or the application note **Allegro Package Designations** on the Allegro website. When applicable, references are provided to industry standards, such as for tape and reel specifications standard package outline designations. These references are provided for informational purposes only, and do not necessarily indicate full conformity with that standard in all respects. No dimensional tolerances are guaranteed or implied for bulk packing.

© 2021, Allegro MicroSystems

Allegro MicroSystems reserves the right to make, from time to time, such departures from the detail specifications as may be required to permit improvements in the performance, reliability, or manufacturability of its products. Before placing an order, the user is cautioned to verify that the information being relied upon is current.

Allegro's products are not to be used in life support devices or system, if a failure of an Allegro product can reasonably be expected to cause the failure of that life support device or system, or to affect the safety or effectiveness of that device or system.

The information included herein is believed to be accurate and reliable. However, Allegro MicroSystems assumes no responsibility for its use; nor for any infringement of patents or other rights of third parties which may result from its use.

Allegro MicroSystems
955 Perimeter Road
Manchester, New Hampshire 03103-3353
U.S.A.
1.603.626.2300 | www.allegromicro.com